


Deep Learning Bundle

Convolutional Neural Network-based inspection libraries



At a Glance

- Set of Deep Learning inspection libraries optimized for machine vision applications
- Performs image classification, supervised or unsupervised segmentation and object localization
- Includes EasyClassify, EasySegment and EasyLocate
- Simple API
- Includes the free Deep Learning Studio application for dataset creation, training and evaluation
- Supports data augmentation and masks
- Compatible with CPU and GPU processing

Benefits

New in Open eVision 23.04

- A new code reader tool ECodeReader allowing to read multiple code types from a single integrated interface
- Deep Learning Studio is now available on Linux ARM-64 platforms
- Neural Network “engines” allow additional devices support (OpenVINO, Tensor RT) and increased speed.
- EasyBarCode2 now supports learning from images to improve its capabilities on similar images.

What Is Deep Learning ?

Neural Networks are computing systems inspired by the biological neural networks that constitute the human brain. Convolutional Neural Networks (CNN) are a class of deep, feed-forward artificial neural networks, most commonly applied to analyzing images.

Deep Learning uses large CNNs to solve complex problems difficult or impossible to solve with so-called conventional computer vision algorithms. Deep Learning algorithms may be easier to use as they typically learn by example. They do not require the user to figure out how to classify or inspect parts. Instead, in an initial training phase, they learn just by being shown many images of the parts to be inspected. After successful training, they can be used to classify parts, or detect and segment defects.

Why Choose Open eVision's Deep Learning Bundle?

- Deep Learning Bundle has been tailored, parametrized and optimized for analyzing images, particularly for machine vision applications.
- Deep Learning Bundle has a simple API and the user can benefit from the power of deep learning technologies with only a few lines of code.

- Try before you buy: Deep Learning Bundle comes with the free Deep Learning Studio training and evaluation application.

EasyClassify, EasySegment and EasyLocate cannot be purchased separately. They are only available as part of the Deep Learning Bundle.

Download and evaluate Deep Learning Bundle using Deep Learning Studio today, and feel free to call Euresys' support should you have any question.

New in Open eVision 22.12

- A new assisted segmentation tool is available in Deep Learning Studio for the EasySegment Supervised annotations. It provides a quick and efficient way to get pixel- perfect annotations.
- EasyFind has been extended to support :
 - Vector learning patterns. This extension is well- suited to find objects with a known geometry.
 - Pattern matching using feature point technology
- EasyBarCode2 and EasyQRCode now support the GS1 symbology.
- EasyMatrixCode2 now supports the Data Matrix Rectangular Extension (ISO/IEC 21471, DMRE).

EasyClassify Description

EasyClassify is the classification tool of Deep Learning Bundle.

EasyClassify requires the user to label training images, that is to tell which ones are good and which ones are bad, or which ones belong to which class. After this learning/training process, the EasyClassify library is able to classify images. For any given image, it returns a list of probabilities, showing the likelihood that the image belongs to each of the classes it has been taught. For example, if the process requires setting apart bad parts from good ones, EasyClassify returns whether each part is good or bad, and with what probability.

EasySegment Unsupervised mode

EasySegment is the segmentation tool of Deep Learning Bundle. EasySegment performs defect detection and segmentation. It identifies parts that contain defects, and precisely pinpoints where they are in the image. The unsupervised mode of EasySegment works by learning a model of what is a “good” sample (i.e. a sample without any defect). This is done by training it only with images of “good” samples. Then, the tool can be used to classify new images as good or defective and segment the defects from these images. By training only with images of good samples, the unsupervised mode of EasySegment is able to perform inspection even when the type of defect is not known beforehand or when defective samples are not readily available.

New in Open eVision 22.08

- EasyLocate Interest Point : New working mode (alternative to EasyLocate Axis Aligned Bounding Box) simplifying the annotation of the dataset and the configuration of the tools when all objects have the same size. A single click is enough to annotate an EasyLocate Interest Point object.
- EasyGauge : New Polygon Gauge in addition to Point, Line, Rectangle, Circle and Wedge gauges.
- Deep Learning tools now supporting GPU processing on NVIDIA Jetson.
- Faster compilation time with simplified C++ headers and reduced calling cost to the Open eVision API.

EasySegment Supervised mode

EasySegment is the segmentation tool of Deep Learning Bundle. EasySegment performs defect detection and segmentation. It identifies parts that contain defects, and precisely pinpoints where they are in the image. The supervised mode of EasySegment works by learning a model of what is a defect and what is a “good” part in an image. This is done by training with images annotated with the expected segmentation. Then, the tool can be used to detect and segment the defects in new images. The supervised mode of EasySegment achieves better precision and can segment more complex defects than the unsupervised mode thanks to the knowledge of the expected segmentation.

EasyLocate Description

EasyLocate is the localization and identification library of Deep Learning Bundle. It is used to locate and identify objects, products, or defects in the image. It has the capability of distinguishing overlapping objects and, as such, EasyLocate is suitable for counting the number of object instances. Two methods are available:

- “EasyLocate Axis Aligned Bounding Box” predicts the bounding box surrounding each object (or defect) it has found in the image and assigns a class label to each of them. It must be trained with images where the objects (or defects) that must be found have been annotated with a bounding box and a class label.
- “EasyLocate Interest Point” predicts the position (as one point, typically the center, but may be otherwise defined) for each object (or defect) it has found in the image and assigns a class label to each of them. All the objects (or defects) in the image must have the same approximate size. It must be trained with images where the objects (or defects) that must be found have simply been annotated with an interest point and a class label. The annotation process is faster with EasyLocate Interest Point as a single click is enough to annotate an object.

Deep Learning Studio

Open eVision includes the free Deep Learning Studio application. This application assists the user during the creation of the dataset as well as the training and testing of the deep learning tool. For EasySegment, Deep Learning Studio integrates an annotation tool and can transform prediction into ground truth annotation. It also allows to graphically configure the tool to fit performance requirements. For example, after training, one can choose a tradeoff between a better defect detection rate or a better good detection rate.

Deep Learning Bundle Feature Comparison

Performance

Deep Learning generally requires significant amounts of processing power, especially during the learning phase. Deep Learning Bundle supports standard CPUs and automatically detects Nvidia CUDA-compatible GPUs in the PC. Using a single GPU typically accelerates the learning and the processing phases by a factor of 100.

Neo Licensing System

- Neo is the new Licensing System of Euresys. It is reliable, state-of-the-art, and is now available to store Open eVision and eGrabber licenses.
- Neo allows you to choose where to activate your licenses, either on a Neo Dongle or in a Neo Software Container. You buy a license, you decide later.
- Neo Dongles offer a sturdy hardware and provide the flexibility to be transferred from a computer to another.
- Neo Software Containers do not need any dedicated hardware, and instead are linked to the computer on which they have been activated.
- Neo ships with its own, dedicated, Neo License Manager, which comes in two flavours: an intuitive, easy to use, Graphical User Interface and a Command Line Interface that allows for easy automation of Neo licensing procedures.

All Open eVision libraries are available for Windows and Linux

- Microsoft Windows 11, 10, 8.1, 7 for x86-64 (64-bit) processor architecture
- Linux for x86-64 (64-bit) and ARMv8-A (64-bit) processor architectures with a glibc version greater or equal to 2.18

Developed with the support of the DG06 Technology Development Department

Applications

Machine Vision for the Electronic Manufacturing Industry

- High speed image acquisition for AOI, 3D SPI, 3D lead/ball inspection machines.
- Very high resolution line-scan image acquisition for Flat Panel Display inspection and solar cell inspection
- PCB inspection
- Mark inspection
- LED inspection

Machine Vision for the General Manufacturing Industries

- High frame rate image acquisition for inspection machines
- Line-scan image acquisition for surface inspection machines
- Line-scan image acquisition for textile inspection
- Presence / Absence check
- Surface analysis
- Assembly inspection

- Code quality verification for label printing machines

Machine Vision for the Printing Industry

- High speed line-scan image acquisition for printing inspection machines

Machine Vision for the Food Inspection Industry

- Food inspection and sorting

Video Acquisition and Recording

- High-frame-rate video acquisition for motion analysis and recording
- Scientific research, hyperspectral imaging

Military & Defense

- Transmission and acquisition of high-definition video over long coaxial cables
- Airborne ISR
- Camera turrets for airborne surveillance or gun turrets
- Unmanned applications, vehicle-based video capture, remote control of UAVs

Video Monitoring, Surveillance & Security

- Transmission and acquisition of high-definition video over long coaxial cables for traffic surveillance, monitoring and control
- Embedded security systems for rail and road transportation, police vehicles

Specifications

Software

Host PC Operating System	• Open eVision is a set of 64-bit libraries that require an Intel compatible processor with the SSE4 instruction set or an ARMv8-A compatible processor. • Open eVision can be used on the following operating systems: – Microsoft Windows 11, 10, 8.1, 7 for x86-64 (64-bit) processor architecture – Linux for x86-64 (64-bit) and ARMv8-A (64-bit) processor architectures with a glibc version greater or equal to 2.18 • Remote connections – Remote connections are allowed using remote desktop, TeamViewer or any other similar software. • Virtual machines – Virtual machines are supported. Microsoft Hyper-V, Oracle VirtualBox and libvirt hypervisors have been successfully tested. – Only the Neo Licensing System is compatible with virtualization. • Minimum requirements: – 2 GB RAM to run an Open eVision application – 8 GB RAM to compile an Open eVision application – Between 100 MB and 2 GB free hard disk space for libraries, depending on selected options.
APIs	• Supported Integrated Development Environments and Programming Languages: – Microsoft Visual Studio 2017 (C++, C#, VB .NET, C++/CLI) – Microsoft Visual Studio 2019 (C++, C#, VB .NET, C++/CLI) – Microsoft Visual Studio 2022 (C++, C#, VB .NET, C++/CLI) – QtCreator 4.15 with Qt 5.12

Ordering Information

Product code - Description	• 4182 - Open Deep Learning Bundle for USB dongle • 4232 - Open Deep Learning Bundle for PAR dongle • 4282 - Open Deep Learning Bundle for soft-based licensing • 4332 - Open eVision Deep Learning Bundle
Optional accessories	• 6512 - eVision/Open eVision USB Dongle (empty) • 6513 - eVision/Open eVision Parallel Dongle (empty) • 6514 - Neo USB Dongle (empty)



EMEA

Euresys SA

Liège Science Park - Rue du Bois Saint-Jean, 20
4102 Seraing - Belgium

Email: sales.europe@euresys.com

EMEA

Sensor to Image GmbH

Lechtorstasse 20
86956 Schongau - Germany

Email: sales.europe@euresys.com

AMERICA

Euresys Inc.

316 Prado Way
Greenville, SC 29607 - United States

Email: sales.americas@euresys.com

ASIA

Euresys Pte. Ltd.

750A Chai Chee Road - #07-15 ESR BizPark @ Chai Chee
Singapore 469001 - Singapore

Email: sales.asia@euresys.com

CHINA

Euresys Shanghai Liaison Office

Unit 802, Tower B, Greenland The Center - No.500 Yunjin Road, Xuhui District
200232 Shanghai - China

Euresys上海联络处

上海市徐汇区云锦路500号绿地汇中心B座802室
200232

Email: sales.china@euresys.com

CHINA

Euresys Shenzhen Liaison Office

Room 1202 - Chinese Overseas Scholars Venture Building
518057 Shenzhen - China

Euresys深圳联络处

深圳南山区留学生创业大厦1期1202
518057

Email: sales.china@euresys.com

JAPAN

Euresys Japan K.K.

Expert Office Shinyokohama - Nisso Dai 18 Building, Shinyokohama 3-7-18, Kohoku
Yokohama 222-0033 - Japan
〒222-0033

神奈川県横浜市港北区新横浜3-7-18 日総第18ビル エキスパートオフィス新横浜

Email: sales.japan@euresys.com

More at www.euresys.com

